



## SCS 12/24V Speed control system for electronic pumps



### Quick Overview

With the control panel for electronic pumps, it is possible to monitor the operation of the pump (run / fail / power / flow and low / high speed) and activate its main functions: on / off, error reset, low speed and high speed. With subsequent low / high button pressures, the best speed can be set based on the viscosity of the transferred liquid. For operation, simply connect the panel to the pump with the supplied 3 m cord or other 4-wire telephone cable and double termination RJ11 / 6. The terminal block on the rear allows control of the pump using external buttons and LEDs. With the USB socket you can access the main pump functionality through software developed by the customer in collaboration with our technical department.

Part n.	Name	Voltage (V)	IP Protection	Bore (mm)	Connector	Dimensions (in)
16520415	SCS	12/24	65	70	RJ11	80x80x46



**RJ11 Black cable with coupler for  
SCS / PCS**